

YA302LH86

by Burndy
Catalog ID: YA302LH86

Pure Cu Compression Terminal, Shrouded Barrel, 2-NEMA Holes, 300 kcmil



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYSEALUG™
Type	Long Barrel, Tin Plated
UPC	781810314050
UPC 12 Digit	7818103140500

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	178 mm
Dimension - Length BB inch	1.25 in
Dimension - Length Overall inch	7.00 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.25 in
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 kcmil
Conductor - Material	Copper

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)