

YA30L24B

by Burndy
Catalog ID: YA30L24B

Prop 65 Notice

COPPER COMPRESSION TERMINAL.



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	1022
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	781810181430
UPC 12 Digit	7818101814300

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	0.83 in
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.65 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.57 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Thread Size	3/8

Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	3/0 (450/#24) DLO
Conductor - Copper DLO Size Range	3/0 (450/#24) DLO
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex G Size Range	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex H Size Range	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex I Size Range	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex K Size Range	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Flex M Size Range	3/0 AWG
Conductor - Copper Solid Size	3/0 AWG
Conductor - Copper Solid Size Range	3/0 AWG
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)