

YA30L2745

by Burndy
Catalog ID: YA30L2745

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, 300 kcmil Code, 300 Navy, 7/8" Stud, 45 Deg Bend, Standard Barrel



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	17;298
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810314265
UPC 12 Digit	7818103142655

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	7/8
Dimension - Height inch	1.75 in
Dimension - Hole Size inch	0.94 in
Dimension - Hole Size mm	24 mm
Dimension - L Length Overall mm	83 mm
Dimension - Length Overall inch	3.29 in
Dimension - N inch	0.88 in

Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1 in
Dimension - Z inch	0.89 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	300 kcmil
Conductor - Material	Copper

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)