



YA30LB90

by Burndy
Catalog ID: YA30LB90

COPPER COMPRESSION TERMINAL.

Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Belled Barrel, Tin Plated
UPC	781810181447
UPC 12 Digit	7818101814477

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	1.15 in
Dimension - D inch	1.08 in
Dimension - Height inch	2.35 in
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - Inside Diameter inch	0.65 in
Dimension - L Length Overall mm	45 mm
Dimension - Length Overall inch	1.78 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1 1/8
Dimension - Z inch	0.55 in

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	300 kcmil
Conductor - Copper Str Size Range	300 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)