

YA30LNT38G1

by Burndy
Catalog ID: YA30LNT38G1

300-SHORT-3/8-.80 NARTNG



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	17;298
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810163962
UPC 12 Digit	7818101639622

Dimensions

Dimension - B Length fraction	1 in
Dimension - B Length inch	1.03 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	1.20 in
Dimension - Hole Size inch	0.40 in
Dimension - Inside Diameter inch	0.65 in
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.97 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	0.82 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	3/8
Dimension - Thread Size	3/8

Dimension - Z inch	0.82 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	300 (91) Navy
Conductor - Copper Str Navy Size Range	300 (91) Navy
Conductor - Copper Str Size	300 kcmil
Conductor - Copper Str Size Range	300 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)