

## YA30LNT516FX

by Burndy  
Catalog ID: YA30LNT516FX

Prop 65 Notice

Cu Tubing Compression Terminal, Narrow Tongue, 1 Hole W/InspWindow,  
250 kcmil Class G,H, 4/0 AWG Class I,K,M, 4/0 (550/#24)DLO, 5/16" Stud,  
Standard Barrel



### Product Details

#### General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810540312
UPC 12 Digit	7818105403122

#### Dimensions

Dimension - B Length inch	1.03 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.49 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	5/16
Physical Attribute - Tongue Angle	Straight

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Material	Copper
----------------------	--------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)