



## YA30LN

by Burndy  
Catalog ID: YA30LN

Prop 65 Notice

HYLUG

## Product Details

### General

Color Code	White
Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810547069
UPC 12 Digit	7818105470699

### Dimensions

Dimension - B Length inch	1.03 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.87 in
Dimension - Pad Width inch	1.20 in
Dimension - Strip Length inch	1 in
Dimension - Stud Size inch	1/2
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Material	Copper
----------------------	--------

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)