

YA30LTC34FX90

by Burndy
Catalog ID: YA30LTC34FX90

Cu Tubing Hylug; 1 Hole with Inspection Window; 250 Flex CLASS G:259
STR CLASS H:427 STR; 600V-35kV; 3/4" stud; Standard; Compression;
Yellow; 90 Degree Bend



Product Details

General

Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810314173
UPC 12 Digit	7818103141733

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Bolt Size fraction	3/4
Dimension - Height inch	1.89 in
Dimension - Hole Size inch	0.81 in
Dimension - Hole Size mm	21 mm
Dimension - L Length Overall mm	52 mm
Dimension - Length Overall inch	2.05 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.20 in

Dimension - Strip Length inch	1-1/16
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex G Size	250 kcmil
Conductor - Copper Flex H Size	250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)