

YA30LTC58FX45

by Burndy
Catalog ID: YA30LTC58FX45

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, 250 Flex Class G,H, 5/8" Stud, Standard Brll; 45 Degree Bend



Product Details

General

| | |
|--------------------------------------|-------------------------|
| Color Code | Yellow |
| Connector Type | Terminal |
| Die Index | 16 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Tin Plated |
| UPC | 781810314210 |
| UPC 12 Digit | 7818103142100 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length inch | 1.03 in |
| Dimension - Bolt Hole Size inch | 0.66 in |
| Dimension - Bolt Size fraction | 5/8 |
| Dimension - Height inch | 1.75 in |
| Dimension - Hole Size inch | 0.69 in |
| Dimension - Hole Size mm | 18 mm |
| Dimension - L Length Overall mm | 72 mm |
| Dimension - Length Overall inch | 2.85 in |
| Dimension - N inch | 0.66 in |
| Dimension - Outside Diameter inch | 0.81 in |

| | |
|-----------------------------------|-----------|
| Dimension - Pad Width inch | 1.20 in |
| Dimension - Strip Length inch | 1-1/16 |
| Dimension - Z inch | 0.67 in |
| Physical Attribute - Tongue Angle | 45 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--------------------------------|-----------|
| Conductor - Copper Flex G Size | 250 kcmil |
| Conductor - Copper Flex H Size | 250 kcmil |
| Conductor - Copper Str Size | 250 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)