

YA312LH89

by Burndy
Catalog ID: YA312LH89

Copper Compression Terminal with shrouded barrel; 2 Holes; 350 KCMIL;
Tin Plated



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYSEALUG™
Type	Shrouded Barrel, Tin Plated
UPC	781810026168
UPC 12 Digit	7818100261688

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length BB inch	1.25 in
Dimension - Length Overall inch	6.75 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.38 in
Dimension - Z inch	0.62 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	350 kcmil
-----------------------------	-----------

Conductor - Material	Copper
----------------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)