

YA312NT38

by Burndy
Catalog ID: YA312NT38

Copper HYLUG™, Double holes W/O insp window, 350 kcmil, 3/8" Stud, Red, 18 or 324 index Tin Plated.



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	18;324
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672761

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2 in
Dimension - Bolt Hole Size inch	0.41 in
Dimension - Bolt Size fraction	3/8
Dimension - L Length Overall mm	114 mm
Dimension - Length Overall inch	4.48 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	2-1/16 in
Dimension - Stud Size inch	3/8 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	350 (91)

Conductor - Copper Str Size	350
Conductor - Copper Str Size Range	350
Conductor Type	<ul style="list-style-type: none">• CU C Str-Size• CU C Str Navy-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)