



YA31AY2N

by Burndy
Catalog ID: YA31AY2N

Prop 65 Notice

HYLUG (ALUMINUM)

Product Details

General

Connector Type	Terminal
Die Index	522
Feature - Barrel Style	Chamfered
Material	Aluminum
Physical Attribute - Number of Crimps Required	3
Physical Attribute - Number of Holes	2
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810106457
UPC 12 Digit	7818101064577

Dimensions

Dimension - B Length inch	3.56 in
Dimension - D inch	3.00 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.86 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.11 in
Dimension - Pad Width inch	1.55 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	350 kcmil
Conductor - AL Str Size Range	350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)