



## YA31L2NT38E16

by Burndy  
Catalog ID: YA31L2NT38E16

Prop 65 Notice

Flex Conductor Standard Barrel Narrow,2 Holes /W/ insp window, 350 kcmil, 3/8 in, 3.51 in L,18 index,Red

## Product Details

### General

Color Code	Red
Connector Type	Terminal
Die Index	18
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810498132

### Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	2.59 in
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.36 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	0.88 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)