

YA31L45

by Burndy
Catalog ID: YA31L45

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 350 kcmil, 1/2" Stud, Short Barrel, Tin Plated, Red, 45 degree bend



Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	18;324
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810020043

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.08 in
Dimension - Height inch	1.85 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	70 mm
Dimension - Length Overall inch	2.75 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1-3/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.55 in

Physical Attribute - Tongue Angle	45 Degree
-----------------------------------	-----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	350 (91) Navy
Conductor - Copper Str Navy Size Range	350 (91) Navy
Conductor - Copper Str Size	350 kcmil
Conductor - Copper Str Size Range	350 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)