



YA31LNT3890

by Burndy
Catalog ID: YA31LNT3890

Prop 65 Notice

1 Hole HYLUG Uninsulated Cu Compression Terminal, Narrow Tongue, 350 kcmil, 600 V - 35 KV, Standard Barri, Red

Product Details

General

| | |
|--------------------------------------|----------------------|
| Color Code | Red |
| Connector Type | Terminal |
| Die Index | 18;324 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| UPC | 781810244272 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-1/16 in |
| Dimension - B Length inch | 1.06 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - D inch | 1.45 in |
| Dimension - Height inch | 1.96 in |
| Dimension - L Length Overall mm | 51 mm |
| Dimension - Length Overall inch | 2.00 in |
| Dimension - N inch | 0.38 in |
| Dimension - Outside Diameter inch | 0.88 in |
| Dimension - Pad Width inch | 0.96 in |
| Dimension - Strip Length inch | 1-1/8 |

| | |
|-----------------------------------|-----------|
| Dimension - Stud Size inch | 3/8 |
| Dimension - Z inch | 1.07 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--|---------------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Navy Size | 350 (91) Navy |
| Conductor - Copper Str Navy Size Range | 350 (91) Navy |
| Conductor - Copper Str Size | 350 kcmil |
| Conductor - Copper Str Size Range | 350 kcmil |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|-----|
| Minimum Pack Quantity | 100 |
|-----------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)