

YA31LTC34FX90

by Burndy
Catalog ID: YA31LTC34FX90

250 kcmil copper flex; standard barrel, 1-hole; 3/4" stud; 90 angle



Product Details

General

| | |
|--------------------------------------|---|
| Color Code | White |
| Connector Type | Terminal |
| Die Index | 17;298 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Tin Plated |
| UPC | 781810314555 |
| UPC 12 Digit | 7818103145555 |

Dimensions

| | |
|---------------------------------|-----------|
| Dimension - B Length fraction | 1-1/16 in |
| Dimension - B Length inch | 1.06 in |
| Dimension - Bolt Hole Size inch | 0.81 in |
| Dimension - Bolt Size fraction | 3/4 |
| Dimension - Height inch | 1.98 in |
| Dimension - Hole Size inch | 0.81 in |
| Dimension - Hole Size mm | 21 mm |
| Dimension - L Length Overall mm | 53 mm |
| Dimension - Length Overall inch | 2.09 in |

| | |
|-----------------------------------|-----------|
| Dimension - N inch | 0.75 in |
| Dimension - Outside Diameter inch | 0.88 in |
| Dimension - Pad Width inch | 1.29 in |
| Dimension - Strip Length inch | 1-1/8 |
| Dimension - Z inch | 0.77 in |
| Physical Attribute - Tongue Angle | 90 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--------------------------------|-----------|
| Conductor - Copper Flex I Size | 250 kcmil |
| Conductor - Copper Flex K Size | 250 kcmil |
| Conductor - Copper Flex M Size | 250 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)