



YA31LTC58FX

by Burndy
Catalog ID: YA31LTC58FX

Prop 65 Notice

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, 250 Kcmil Flex Class I,K,M, 5/8" Stud, Standard Brrl

Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	17;298
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810035627
UPC 12 Digit	7818100356277

Dimensions

Dimension - B Length fraction	1-1/16 in
Dimension - B Length inch	1.06 in
Dimension - Bolt Hole Size inch	0.69 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17 mm
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	1-1/8
Dimension - Stud Size inch	5/8
Dimension - Z inch	0.67 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Flex I Size	250 kcmil
Conductor - Copper Flex K Size	250 kcmil
Conductor - Copper Flex M Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)