

YA322NU

by Burndy
Catalog ID: YA322NU

Prop 65 Notice

Copper Compression Lug, Blank Tongue w/o Inspection Window, 400 kcmil, 3/8" Min, 1/2" Max. Stud, Long Barrel, Tin Plated



Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	19;470
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	0
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810505601
UPC 12 Digit	7818105056011

Dimensions

Dimension - B Length fraction	2-1/8 in
Dimension - B Length inch	2.12 in
Dimension - L Length Overall mm	149 mm
Dimension - Length Overall inch	5.85 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	2-3/16
Dimension - Stud Size inch	3/8 in, 7/16 in, 1/2 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	400 kcmil
-----------------------------	-----------

Conductor - Material	Copper
----------------------	--------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)