

YA32A3

by Burndy
Catalog ID: YA32A3

Prop 65 Notice

Aluminum Compression Lug, 2 Hole w/o Inspection Window, 400 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing.

Conductor Type: Aluminum, Tongue Angle: Straight



Product Details

General

Application	For Aluminum And Copper Conductors
Color Code	Green
Connector Type	Terminal
Die Index	472
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-A, Dual Rated
UPC	781810756003
UPC 12 Digit	7818107560033

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.26 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.11 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	156 mm
Dimension - Length Overall inch	6.15 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2

Dimension - Stud Size inch	1/2
Dimension - Thread Size	1/2
Dimension - Z inch	0.73 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	400 kcmil
Conductor - AL Str Size Range	400 kcmil
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)