

YA32A6

by Burndy
Catalog ID: YA32A6

Prop 65 Notice

Uninsul Al Comp Terminal, 1 Hole, 400 kcmil, 600 V-35 kV, 1/2" Stud, Closed bbl, Green, 472 Index, For Al & Cu Cond, Color Coded End Cap.

UL Listed 90 DEG C, 600 V - 35 KV, Tongue Angle: Straight



Product Details

General

Application	For Aluminum & Copper Conductors
Color Code	Green
Connector Type	Terminal
Die Index	472
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	YA-L-NT
UPC	781810101407
UPC 12 Digit	7818101014077

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.26 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.88 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	125 mm
Dimension - Length Overall inch	4.92 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.62 in

Dimension - Thread Size	1/2
Dimension - Z inch	1.00 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	400 kcmil
Conductor - AL Str Size Range	400 kcmil
Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)