



YA32LNT11MMSL

by Burndy
Catalog ID: YA32LNT11MMSL

Copper HYLUGTM, Single Hole /W/ insp window, 400 kcmil, 1/2" stud, 19 index, Blue, Tin Plated

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	19;470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810463642

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Inside Diameter inch	0.76 in
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.21 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	0.96 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	400 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy
Conductor - Copper Str Size	400 kcmil

Conductor - Copper Str Size Range	400 kcmil
-----------------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)