



YA32LNT3890

by Burndy
Catalog ID: YA32LNT3890

1 Hole HYLUG Cu Compression Terminal, Narrow Tongue, 400 kcmil, 3/8" stud, Blue, 19 or 470 Index, Wire Strip Length - 1-1/4" L

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	19;470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810496787

Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Diameter Min Size inch	0.85 in
Dimension - Height inch	2.19 in
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.45 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/4
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Conductor - Copper Str Navy Size	400 (127) Navy
Conductor - Copper Str Navy Size Range	400 (127) Navy
Conductor - Copper Str Size	400 kcmil
Conductor - Copper Str Size Range	400 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)