

# YA32LNT38FX

by Burndy  
Catalog ID: YA32LNT38FX

Prop 65 Notice

1 Hole, Narrow Tongue, Standard Barrel Cu Compr Terminal, 313.1 kcmil,  
600 V - 35 KV, 3/8" stud, Red, 18 Index



## Product Details

### General

Color Code	Red
Connector Type	Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810355732

### Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - D inch	0.83 in
Dimension - L Length Overall mm	68 mm
Dimension - Length Overall inch	2.68 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-1/4
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size	313.1 (775/#24) DLO
Conductor - Copper DLO Size Range	313.1 (775/#24) DLO
Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex G Size Range	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex H Size Range	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex I Size Range	300 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex K Size Range	300 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Flex M Size Range	300 kcmil

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	50
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)