



## YA32LTC34FX90

by Burndy  
Catalog ID: YA32LTC34FX90

Cu Compression Terminal, 1 Hole W/InspWindow, 300 kcmil Flex,  
313.1(775/#24)DLO, 3/4" Stud, 90 Deg Bent, Standard Barrel

### Product Details

#### General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810049167
UPC 12 Digit	7818100491677

#### Dimensions

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

#### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Material	Copper

#### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

#### Logistics

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)