

# YA32LTC38FXG1

by Burndy  
Catalog ID: YA32LTC38FXG1

Copper Tubing Compression Terminal, 1 Hole,electro-Tin  
Plated,accommodates 300 kcmil



## Product Details

### General

Connector Type	Terminal
Die Index	1026
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810093191
UPC 12 Digit	7818100931911

### Dimensions

Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.19 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.76 in
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	1-1/4
Dimension - Z inch	0.73 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex G Size	300 kcmil
Conductor - Copper Flex G Size Range	300 kcmil
Conductor - Copper Flex H Size	300 kcmil
Conductor - Copper Flex H Size Range	300 kcmil
Conductor - Copper Flex I Size	300 kcmil
Conductor - Copper Flex I Size Range	300 kcmil
Conductor - Copper Flex K Size	300 kcmil
Conductor - Copper Flex K Size Range	300 kcmil
Conductor - Copper Flex M Size	300 kcmil
Conductor - Copper Flex M Size Range	300 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)