



## YA32TC58FXB

by Burndy  
Catalog ID: YA32TC58FXB

Prop 65 Notice

COPPER COMPRESSION TERMINAL.

### Product Details

#### General

Color Code	Red
Connector Type	Terminal
Die Index	18
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810101360
UPC 12 Digit	7818101013600

#### Dimensions

Dimension - B Length fraction	2-5/16 in
Dimension - B Length inch	2.32 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	110 mm
Dimension - Length Overall inch	4.34 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	2-1/4
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	313.1 (775/#24)
Conductor - Copper DLO Size Range	313.1 (775/#24)
Conductor - Copper Flex G Size	313.1
Conductor - Copper Flex G Size Range	313.1
Conductor - Copper Flex H Size	313.1
Conductor - Copper Flex H Size Range	313.1
Conductor - Copper Flex I Size	313.1
Conductor - Copper Flex I Size Range	313.1
Conductor - Copper Flex K Size	313.1
Conductor - Copper Flex K Size Range	313.1
Conductor - Copper Flex M Size	313.1
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)