



YA3390

by Burndy
Catalog ID: YA3390

Copper Tubing Compression Terminal, 1 Hole, Tin Plated, 450 kcmil

Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	326;538
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810314906
UPC 12 Digit	7818103149066

Dimensions

Dimension - B Length fraction	2-1/8 in
Dimension - B Length inch	2.13 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Height inch	3.26 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in

Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.01 in
Dimension - Pad Width inch	1.48 in
Dimension - Strip Length inch	2-5/16
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	450 kcmil
Conductor - Material	Copper

Certifications and Compliance

Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)