

# YA342LH119TN

by Burndy  
Catalog ID: YA342LH119TN

Tin-plated, CU 2-hole NEMA compression terminal with shrouded barrel for terminating insulated CU conductor to transformers and other equipment, 6.50 IN L



## Product Details

### General

Connector Type	Terminal
Die Index	1027
Feature - Barrel Style	Shrouded
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Shrouded Barrel, Tin Plated
UPC	781810025994
UPC 12 Digit	7818100259944

### Dimensions

Dimension - B Length fraction	1-9/16 in
Dimension - B Length inch	1.57 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	165 mm
Dimension - Length BB inch	1.00 in
Dimension - Length Overall inch	6.50 in
Dimension - N inch	0.53 in
Dimension - Pad Width inch	1.52 in
Dimension - Z inch	0.54 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Flex K Size	350 kcmil
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)