

YA34A2NG2TN

by Burndy
Catalog ID: YA34A2NG2TN

HYLUG - TIN PLATED



Product Details

General

| | |
|--------------------------------------|----------------------|
| Connector Type | Terminal |
| Die Index | 300 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Aluminum |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Tongue Type | Standard |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| UPC | 781810178249 |
| UPC 12 Digit | 7818101782499 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 4 in |
| Dimension - B Length inch | 4.00 in |
| Dimension - D inch | 3.04 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Hole Size mm | 14 mm |
| Dimension - Inside Diameter inch | 0.85 in |
| Dimension - L Length Overall mm | 217 mm |
| Dimension - Length Overall inch | 8.53 in |
| Dimension - N inch | 0.63 in |
| Dimension - Outside Diameter inch | 1.32 in |
| Dimension - Pad Width inch | 1.83 in |
| Dimension - Z inch | 0.66 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------|-------|
| Rating - KVA | 35 kV |
|--------------|-------|

| | |
|--------------------------|-------|
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - AL Str Size | 500 kcmil |
| Conductor - AL Str Size Range | 500 kcmil |
| Conductor - Copper Str Size | 500 kcmil |
| Conductor - Copper Str Size Range | 500 kcmil |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)