



## YA34A390

by Burndy  
Catalog ID: YA34A390

Prop 65 Notice

UNINSULATED ALUMINUM COMPRESSION TERMINAL, 1-HOLE  
DESIGNUL Listed 90° C600 Volts to 35 KV.

## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	300
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810178256
UPC 12 Digit	7818101782566

### Dimensions

Dimension - B Length fraction	2-5/16 in
Dimension - B Length inch	2.34 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.15 in
Dimension - Height inch	4.59 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Pad Width inch	1.62 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.77 in

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)