

YA34A3NT119

by Burndy
Catalog ID: YA34A3NT119

Al Tube Uninsulated Compression Terminal, Narrow Tongue, 2 Holes, 500 kcmil Cu/Al, 1/2" Stud, 1.19" Tongue Width



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	300
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810270653
UPC 12 Digit	7818102706533

Dimensions

Dimension - B Length fraction	2-5/16 in
Dimension - B Length inch	2.34 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.15 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.80 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.32 in
Dimension - Pad Width inch	1.19 in
Dimension - Thread Size	1/2
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)