



## YA34CG14

by Burndy  
Catalog ID: YA34CG14

Prop 65 Notice

500 kcmil; cast tongue

## Product Details

### General

Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Silver
Temperature Rating	194
Type	Standard Barrel, Tin Plated
UPC	781810489222
UPC 12 Digit	781810489222

### Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	2.00 in
Dimension - Z inch	1.88 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)