

# YA34G30

by Burndy  
Catalog ID: YA34G30

HYLUG-1 HOLE-SKIVED-UNTR,Copper Tubing Compression Terminal,Tin Plated,350 kcmil



## Product Details

### General

Color Code	Brown
Connector Type	Terminal
Die Index	1027
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	N
Plating Type	Unplated
Trade Name	HYLUG™
UPC	781810182260
UPC 12 Digit	7818101822600

### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	79 mm
Dimension - Length Overall inch	3.12 in
Dimension - N inch	0.44 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.54 in
Dimension - Z inch	0.44 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex H Size	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Str Size	350 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	6
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)