



## YA34L2NTC38FX

by Burndy  
Catalog ID: YA34L2NTC38FX

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 373.7 Flex, 3/8" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Tin Plated

### Product Details

#### General

Color Code	Blue
Connector Type	Terminal
Die Index	19;470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810044063
UPC 12 Digit	7818100440633

#### Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	118 mm
Dimension - Length Overall inch	4.63 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	373.7 (925/#24) DLO
Conductor - Copper DLO Size Range	373.7 (925/#24) DLO
Conductor - Copper Flex G Size	350 kcmil
Conductor - Copper Flex G Size Range	350 kcmil
Conductor - Copper Flex H Size	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 kcmil
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex K Size	350 kcmil
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex M Size	350 kcmil
Conductor - Copper Flex M Size Range	350 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)