



YA34L2TC12FX

by Burndy
Catalog ID: YA34L2TC12FX

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 373.7 Flex, 1/2" Stud, 1-1/4" Stud Hole Spacing, Short Barrel, Tin Plated

Product Details

General

Color Code	Blue
Connector Type	Terminal
Die Index	19;470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018989
UPC 12 Digit	7818100189899

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.38 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	373.7 (925/#24) DLO
Conductor - Copper DLO Size Range	373.7 (925/#24) DLO
Conductor - Copper Flex G Size	350 kcmil
Conductor - Copper Flex G Size Range	350 kcmil
Conductor - Copper Flex H Size	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 kcmil
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex K Size	350 kcmil
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex M Size	350 kcmil
Conductor - Copper Flex M Size Range	350 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	40
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)