

YA34T4

by Burndy
Catalog ID: YA34T4

Cu Compression Terminal, 1 Hole, 500 kcmil, 0.437" Hole Dia.



Product Details

General

Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810182505
UPC 12 Digit	7818101825055

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.50 in
Dimension - D inch	1.50 in
Dimension - Hole Size inch	0.44 in
Dimension - Hole Size mm	11 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	111 mm
Dimension - Length Overall inch	4.38 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.52 in
Dimension - Z inch	0.71 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)