

YA34T8

by Burndy
Catalog ID: YA34T8

Prop 65 Notice

Cu Terminal, 1 Hole, 500 kcmil, 0.56" HoleSize, Tin Plated, Brown, 299/20 Index.

Cu Terminal, 1 Hole, 500 kcmil, 0.56 IN HoleSize, Tin Plated, Brown, 299/20 Index



Product Details

General

Application	For termination of wires
Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Terminal
UPC	781810087305
UPC 12 Digit	7818100873055

Dimensions

Dimension - B Length fraction	2-1/4 in
Dimension - B Length inch	2.25 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	114 mm
Dimension - Length Overall inch	4.47 in
Dimension - N inch	0.75 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	1.55 in
Dimension - Z inch	0.77 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)