

# YA362NT12

by Burndy  
Catalog ID: YA362NT12

Prop 65 Notice

Copper HYLUGTM ,2 holes W/O insp window,600 kcmil,1/2" stud,22 or 472 index,Green,Tin Plated



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	22;472
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810672846

### Dimensions

Dimension - B Length fraction	2-11/16 in
Dimension - B Length inch	2.69 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - Bolt Size fraction	1/2
Dimension - L Length Overall mm	167 mm
Dimension - Length Overall inch	6.59 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.12 in
Dimension - Strip Length inch	2-3/4 in
Dimension - Stud Size inch	1/2 in
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	600

Conductor - Copper Str Size Range	600
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)