



YA36L2NTCFX

by Burndy
Catalog ID: YA36L2NTCFX

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 444.4 Flex, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Tin Plated.

UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight

Product Details

General

Application	For Flex Conductor
Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021347
UPC 12 Digit	7818100213477

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	133 mm
Dimension - Length Overall inch	5.24 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	1-3/8

Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444.4 (1100/#24) DLO
Conductor - Copper DLO Size Range	444.4 (1100/#24) DLO
Conductor - Copper Flex G Size	450 kcmil
Conductor - Copper Flex G Size Range	450 kcmil
Conductor - Copper Flex H Size	450 kcmil
Conductor - Copper Flex H Size Range	450 kcmil
Conductor - Copper Flex I Size	450 kcmil
Conductor - Copper Flex I Size Range	450 kcmil
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex K Size Range	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Copper Flex M Size Range	450 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)