

YA36L2TC38

by Burndy
Catalog ID: YA36L2TC38

Prop 65 Notice

Cu compression tubular terminals-code conductor, 2 holes/W/ insp window, 600 kcmil, 3/8" stud, Green, 22 or 472 index.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Wire Strip Length: 1-3/4 IN, Finish: Electro-Tin Plated, Temperature Rating: 90 DEG C, Die Index: 22, Tongue Angle: Straight, Color Code: Green, Tools, Die Set Catalog Number, And (number Of Crimps): Hydraulic: Y35, Y39, Y750, PAT750 Tool, U36RT, U32ART Die, (2), Y46 Tool, U36RT, U32ART Die With PUADP-1 Adapter, (2), Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), Conductor Type: Commercial Stranded Copper



Product Details

General

Application	For Code Conductor
Color Code	Green
Connector Type	Terminal
Die Index	22;472
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Sub Brand	HYDENT
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810020968
UPC 12 Digit	7818100209688

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	107 mm
Dimension - Length Overall inch	4.23 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.19 in

Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	1-3/4
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.52 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	600 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)