



YA36LTC38FX

by Burndy
Catalog ID: YA36LTC38FX

Prop 65 Notice

Cu Comp Terminal Flex Cond, Bvl Entry, 1 Hole/W/InspWindow, 444.4 kcmil(1100/#24)DLO, 450 kcmil Flex, 600 V-35 kV, 3/8" Stud, Std bbl.

UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight

Product Details

General

Application	For Flex Conductor
Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810101414
UPC 12 Digit	7818101014144

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.23 in
Dimension - N inch	0.50 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	1-3/8
Dimension - Z inch	0.51 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	444.4 (1100/#24) DLO
Conductor - Copper DLO Size Range	444.4 (1100/#24) DLO
Conductor - Copper Flex G Size	450 kcmil
Conductor - Copper Flex G Size Range	450 kcmil
Conductor - Copper Flex H Size	450 kcmil
Conductor - Copper Flex H Size Range	450 kcmil
Conductor - Copper Flex I Size	450 kcmil
Conductor - Copper Flex I Size Range	450 kcmil
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex K Size Range	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Copper Flex M Size Range	450 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)