



## YA36LTC58FX45

by Burndy  
Catalog ID: YA36LTC58FX45

450 kcmil flex; 5/8" stud; standard barrel; 45 angle

### Product Details

#### General

Color Code	Brown
Connector Type	Terminal
Die Index	20;299
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810315422
UPC 12 Digit	7818103154222

#### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Height inch	2.48 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	89 mm
Dimension - Length Overall inch	3.51 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	1-3/8
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	45 Degree

#### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper DLO Size	444.4 (1100/#24) DLO
Conductor - Copper DLO Size Range	444.4 (1100/#24) DLO
Conductor - Copper Flex G Size	450 kcmil
Conductor - Copper Flex G Size Range	450 kcmil
Conductor - Copper Flex H Size	450 kcmil
Conductor - Copper Flex H Size Range	450 kcmil
Conductor - Copper Flex I Size	450 kcmil
Conductor - Copper Flex I Size Range	450 kcmil
Conductor - Copper Flex K Size	450 kcmil
Conductor - Copper Flex K Size Range	450 kcmil
Conductor - Copper Flex M Size	450 kcmil
Conductor - Copper Flex M Size Range	450 kcmil
Conductor - Material	Copper

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)