

# YA36LTC78270

by Burndy  
Catalog ID: YA36LTC78270

Prop 65 Notice

One Hole HYLUG Code Conductor STD Barrel, 600 kcmil, 600 V- 35 KV,  
7/8" stud, 2.40" L, Green



## Product Details

### General

Color Code	Green
Connector Type	Terminal
Die Index	22;472
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810413081
UPC 12 Digit	7818104130811

### Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.91 in
Dimension - Bolt Size fraction	7/8
Dimension - Height inch	3.66 in
Dimension - Hole Size inch	0.94 in
Dimension - Hole Size mm	24 mm
Dimension - L Length Overall mm	61 mm
Dimension - Length Overall inch	2.40 in
Dimension - N inch	0.88 in
Dimension - Outside Diameter inch	1.19 in
Dimension - Pad Width inch	1.74 in
Dimension - Strip Length inch	1-7/16
Dimension - Z inch	1.07 in

Physical Attribute - Tongue Angle	90 Degree
-----------------------------------	-----------

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	600 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)