



## YA372N

by Burndy  
Catalog ID: YA372N

Prop 65 Notice

Copper Two Hole HYLUG - Long Barrel ,Straight Pad for 650 kcmil,1/2" Bolt Hole with 1-3/4" Spacing,Tin Plated,Color: Orange,Die Index: 23.

Accommodates Stranded cable, With Inspection window, Long barrel

## Product Details

### General

Application	For termination
Color Code	Orange
Connector Type	Terminal
Die Index	23
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810032763
UPC 12 Digit	7818100327633

### Dimensions

Dimension - B Length fraction	2-13/16 in
Dimension - B Length inch	2.81 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.74 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.23 in
Dimension - Pad Width inch	1.80 in
Dimension - Strip Length inch	2-7/8
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.64 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	650
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	20
-----------------------	----

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)