



YA37L90

by Burndy
Catalog ID: YA37L90

Copper Compression Terminal,,1 Hole,Tin-Electro Plated,90 Degree

Product Details

General

Color Code	Orange
Connector Type	Terminal
Die Index	23
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810315606
UPC 12 Digit	7818103156066

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.39 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - Bolt Size fraction	5/8
Dimension - Height inch	2.73 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.14 in

Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	1.23 in
Dimension - Pad Width inch	1.80 in
Dimension - Strip Length inch	1-15/16
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	650
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)