

YA38ENT12FX

by Burndy
Catalog ID: YA38ENT12FX

Prop 65 Notice

Hylug; 535.3 kcmil; 1.35 in L; 4.82 in W



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810426241

Dimensions

Dimension - B Length fraction	2-13/16 in
Dimension - B Length inch	2.81 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.08 in
Dimension - Inside Diameter inch	0.98 in
Dimension - L Length Overall mm	122 mm
Dimension - Length Overall inch	4.82 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.35 in
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Flex G Size	500
Conductor - Copper Flex G Size Range	500
Conductor - Copper Flex H Size	500
Conductor - Copper Flex H Size Range	500
Conductor - Copper Flex I Size	500
Conductor - Copper Flex I Size Range	500
Conductor - Copper Flex K Size	500
Conductor - Copper Flex K Size Range	500
Conductor - Copper Flex M Size	500

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)