



YA38L2NNTFX

by Burndy
Catalog ID: YA38L2NNTFX

Prop 65 Notice

Flex Conductor Standard Barrel Narrow, 535.3 kcmil 1325/24 500 Flex, 1/2 in, 5.35 in L.

UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Tongue Angle: Straight

Product Details

General

Application	For Flex Conductor
Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YAV-L-NTFX
UPC	781810034743

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.03 in
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.35 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.63 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.65 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	535.3 (1325/#24) DLO
Conductor - Copper DLO Size Range	535.3 (1325/#24) DLO
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex G Size Range	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex H Size Range	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex I Size Range	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Copper Flex M Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)