

# YA38L2NTCFX45

by Burndy  
Catalog ID: YA38L2NTCFX45

Prop 65 Notice

Cu Comp Terminal, 2 Holes W/InspWindow, 535.3 (1325/#24) DLO (500 kcmil Flex), 1/2" Stud, 1.75" Spacing, 45 Deg Bent, Standard Brll



## Product Details

### General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810021354
UPC 12 Digit	7818100213544

### Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	2.60 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	135 mm
Dimension - Length Overall inch	5.30 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1-7/16

Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	45 Degree

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	535.3 (1325/#24) DLO
Conductor - Copper DLO Size Range	535.3 (1325/#24) DLO
Conductor - Copper Flex G Size	500 kcmil
Conductor - Copper Flex G Size Range	500 kcmil
Conductor - Copper Flex H Size	500 kcmil
Conductor - Copper Flex H Size Range	500 kcmil
Conductor - Copper Flex I Size	500 kcmil
Conductor - Copper Flex I Size Range	500 kcmil
Conductor - Copper Flex K Size	500 kcmil
Conductor - Copper Flex K Size Range	500 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Copper Flex M Size Range	500 kcmil
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)