



YA38LTC38FX45

by Burndy
Catalog ID: YA38LTC38FX45

Prop 65 Notice

Cu compression One Hole Flex conductor std barrl, with insp window, 500 kcmil FLEX, 3/8 " stud, 3.29" L, 1.84" W, 45 Degree, Tin Plating

Product Details

General

| | |
|--------------------------------------|-----------------------------|
| Color Code | Pink |
| Connector Type | Terminal |
| Die Index | L99 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810298343 |
| UPC 12 Digit | 7818102983433 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-7/16 in |
| Dimension - B Length inch | 1.45 in |
| Dimension - Bolt Hole Size inch | 0.39 in |
| Dimension - Bolt Size fraction | 3/8 |
| Dimension - Height inch | 2.60 in |
| Dimension - Hole Size inch | 0.40 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 84 mm |
| Dimension - Length Overall inch | 3.29 in |
| Dimension - N inch | 0.50 in |
| Dimension - Outside Diameter inch | 1.25 in |
| Dimension - Pad Width inch | 1.84 in |
| Dimension - Strip Length inch | 1-7/16 |
| Dimension - Z inch | 0.52 in |
| Physical Attribute - Tongue Angle | 45 Degree |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--------------------------------------|----------------------|
| Conductor - Copper DLO Size | 535.3 (1325/#24) DLO |
| Conductor - Copper DLO Size Range | 535.3 (1325/#24) DLO |
| Conductor - Copper Flex G Size | 500 kcmil |
| Conductor - Copper Flex G Size Range | 500 kcmil |
| Conductor - Copper Flex H Size | 500 kcmil |
| Conductor - Copper Flex H Size Range | 500 kcmil |
| Conductor - Copper Flex I Size | 500 kcmil |
| Conductor - Copper Flex I Size Range | 500 kcmil |
| Conductor - Copper Flex K Size | 500 kcmil |
| Conductor - Copper Flex K Size Range | 500 kcmil |
| Conductor - Copper Flex M Size | 500 kcmil |
| Conductor - Copper Flex M Size Range | 500 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 20 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)