

YA38L

by Burndy
Catalog ID: YA38L

Prop 65 Notice

Copper Tubing Terminal, 700 kcmil, 5/8 IN Stud, 400 Index



Product Details

General

| | |
|--------------------------------------|---|
| Color Code | Pink |
| Connector Type | Terminal |
| Die Index | 400 |
| Feature - Barrel Style | <ul style="list-style-type: none"> • Chamfered • Skived |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810521717 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 1-7/16 in |
| Dimension - B Length inch | 1.45 in |
| Dimension - Bolt Hole Size inch | 0.66 in |
| Dimension - Bolt Size fraction | 5/8 |
| Dimension - D inch | 1.33 in |
| Dimension - Hole Size mm | 18 mm |
| Dimension - L Length Overall mm | 93 mm |
| Dimension - Length Overall inch | 3.66 in |
| Dimension - N inch | 0.66 in |
| Dimension - Outside Diameter inch | 1.25 in |
| Dimension - Pad Width inch | 1.84 in |
| Dimension - Strip Length inch | 1-15/16 |
| Dimension - Stud Size fraction | 5/8 |
| Dimension - Stud Size inch | 5/8 |
| Dimension - Z inch | 0.67 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - Copper DLO Size Range | N/A |
| Conductor - Copper Str Size | 700 kcmil |
| Conductor - Copper Str Size Range | 700 kcmil |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 6 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)